




Smart Membrane Solutions
Putting Process Managers at Ease

Permeate Hoses



Contact Smart Membrane Solutions:



+64 3 741 1808



info@smartmembranesolutions.co.nz



PO Box 148, Rolleston 7643, New Zealand




www.smartmembranesolutions.co.nz

Product features

Smart Membrane Solutions (SMS) permeate hoses are better by design. Utilising over 10 years of experience in plant design SMS permeate hoses are designed with the end user in mind. Features include:

- ✘ Flexible - allowing for ease of plant maintenance, disassembly, and reassembly.
- ✘ Sanitary sample point options - permeate samples can be taken and analysed for protein levels.
- ✘ Visibility - visible monitoring for cloudy permeate to indicate membrane effectiveness.
- ✘ Detection - early identification of leaking membranes, which can prevent significant costs by reduction of protein losses.

Product details



Tri Ferrule Size	Sample Point	Permeate Hose Length	Product Code
1.5"	Yes	300 mm - 25 mm diameter	1.5-TRI-BKSP-25-300
1.5"	Yes	450 mm - 25 mm diameter	1.5-TRI-BKSP-25-450
2.0"	Yes	300 mm - 25 mm diameter	2.0-TRI-BKSP-25-300
2.0"	Yes	450 mm - 25 mm diameter	2.0-TRI-BKSP-25-450
1.5"	No	300 mm - 25 mm diameter	1.5-TRI-BKBK-25-300
1.5"	No	450 mm - 25 mm diameter	1.5-TRI-BKBK-25-450
2.0"	No	300 mm - 25 mm diameter	2.0-TRI-BKBK-25-300
2.0"	No	450 mm - 25 mm diameter	2.0-TRI-BKBK-25-450